

CDC Design Layout

GlueX-doc-979 (version 2)

Curtis A. Meyer
Yves Van Haarlem
Gary Wilkin
Carnegie Mellon University

Updated July 2008

Abstract

This document is a summary of the design parameters of the CDC.
The design described in this report is for a 150 *cm* long version.

1 List of Design Parameters

Table 1: Geometry

Active volume inner radius:	10.18 <i>cm</i>
Active volume outer radius:	55.42 <i>cm</i>
Active length:	150 <i>cm</i>
Chamber assembly outer radius:	60.0 <i>cm</i>
Axial layers (1-3):	10.16 to 15.32 <i>cm</i>
Stereo layers (4-7):	15.5 to 22.45 <i>cm</i>
Axial layers (8-12):	23.9 to 32.63 <i>cm</i>
Stereo layers (13-16):	32.81 to 39.76 <i>cm</i>
Axial layers (17-24):	40.81 to 55.42 <i>cm</i>
Thickness per layer (g/cm ²):	0.051
Thickness per layer (rad. lengths):	0.0014
Thickness per 24 layers (rad. lengths):	0.035

Table 2: Material

Gas (at 1 at.):	<i>Ar/CO₂</i> 90/10
Gas (at 1 at.):	<i>Ar/CO₂/CH₄</i> 80/10/10 (possibly)
Number of cables :	3090/24 = 130
(50-conductor shielded ribbon cables)	
Positioning accuracy of sense wires (x,y):	10 μm
Positioning accuracy of package (z):	0.5 <i>mm</i>
Thickness of inner shell (g/cm ²):	0.162
Thickness of inner shell (rad. lengths):	0.0067
Thickness of outer shell (g/cm ²):	1.02 <i>cm</i> of fiberglass
Thickness of outer shell (rad. lengths):	0.031
Strawtube (diameter):	1.6 <i>cm</i>
Strawtube (material):	Aluminized Kapton
Strawtube (thickness):	100(5) μm Kapton(Al)
Number of sense wires (20 micron gold-plated W):	3090 \pm 1.5%
Upstream Endplate:	0.9525 <i>cm</i> Al (3/8 plate)
Downstream Endplate:	0.4 <i>cm</i> Carbon Fiber
Upstream Feedthrus:	Al
Downstream Feedthrus:	Delrin
Plenums:	Plexiglas

Table 3: Location active area

Upstream gas plenum:	-3 <i>cm</i>
Upstream active volume:	17 <i>cm</i>
Downstream active volume:	167 <i>cm</i>
Downstream gas plenum:	177 <i>cm</i>

Table 4: dE/dX capability

Sense wires:	YES
Momentum Range:	$p \leq 450 MeV/c$

Table 5: Operation:

Nominal operating voltage (sense):	+1900 <i>V</i>
Nominal gas gain:	5×10^4
Gas flow:	5/ <i>day</i>

Table 6: Preamplifier and Readout

Nominal gain:	5×10^4
Noise level:	
Rise time:	$\sim 50 \text{ ns}$
Tail compensation:	YES
Cable length to post-amp:	30 m
Discriminator output:	NO
Sense wires:	125 MHz FADCs

Table 7: Calibration and Resolution

Sense wires (selected charge):	electronic pulser
Perpendicular to wire (σ):	$150 \mu\text{m}$
z-position from stereo (σ):	2 mm
z-position from charge division:	8 cm

Layer	Channels	Radius (cm) (center)	Radius (cm) (end plate)	Stereo (radians)	Δr
1	43	10.984	10.984	0.000	10.984
2	50	12.769	12.769	0.000	1.785
3	57	14.555	14.555	0.000	1.785
4	63	16.174	17.992	0.105	1.619
5	70	17.969	19.622	0.105	1.796
6	77	19.765	21.279	-0.105	1.796
7	84	21.561	22.956	-0.105	1.796
8	98	25.015	25.015	0.000	3.454
9	105	26.801	26.801	0.000	1.786
10	112	28.588	28.588	0.000	1.786
11	119	30.374	30.374	0.000	1.786
12	126	32.160	32.160	0.000	1.786
13	132	33.877	34.782	0.105	1.717
14	139	35.673	36.533	0.105	1.796
15	146	37.469	38.289	-0.105	1.796
16	153	39.265	40.049	-0.105	1.796
17	165	42.113	42.113	0.000	2.847
18	172	43.899	43.899	0.000	1.786
19	179	45.686	45.686	0.000	1.786
20	186	47.472	47.472	0.000	1.786
21	193	49.258	49.258	0.000	1.786
22	200	51.045	51.045	0.000	1.786
23	207	52.831	52.831	0.000	1.786
24	214	54.618	54.618	0.000	1.786

Table 8: This table shows the number of channels in each layer of the 150 *cm* long version of the CDC. The radius at the center is the wire location half-way between the two end plates. The radius at the endplates is where the wire goes through the end plate. For axial layers, both radii are the same. For the stereo layers, the radius at the endplate is larger than it is at the center.

Layer	Tubes	$\Delta\phi$	x_u	y_u	x_c	y_c	x_d	y_d
1	43	0.1461	10.9840	0.0000	10.9840	0.0000	10.9840	0.0000
2	50	0.1257	12.7691	0.0000	12.7691	0.0000	12.7691	0.0000
3	57	0.1102	14.5546	0.0000	14.5546	0.0000	14.5546	0.0000
4	63	0.0997	16.1737	7.8813	16.1737	0.0000	16.1737	-7.8813
5	70	0.0898	17.9694	7.8813	17.9694	0.0000	17.9694	-7.8813
6	77	0.0816	19.7652	-7.8813	19.7652	0.0000	19.7652	7.8813
7	84	0.0748	21.5610	-7.8813	21.5610	0.0000	21.5610	7.8813
8	98	0.0641	25.0152	0.0000	25.0152	0.0000	25.0152	0.0000
9	105	0.0598	26.8015	0.0000	26.8015	0.0000	26.8015	0.0000
10	112	0.0561	28.5877	0.0000	28.5877	0.0000	28.5877	0.0000
11	119	0.0528	30.3740	0.0000	30.3740	0.0000	30.3740	0.0000
12	126	0.0499	32.1603	0.0000	32.1603	0.0000	32.1603	0.0000
13	132	0.0476	33.8769	7.8813	33.8769	0.0000	33.8769	-7.8813
14	139	0.0452	35.6731	7.8813	35.6731	0.0000	35.6731	-7.8813
15	146	0.0430	37.4693	-7.8813	37.4693	0.0000	37.4693	7.8813
16	153	0.0411	39.2655	-7.8813	39.2655	0.0000	39.2655	7.8813
17	165	0.0381	42.1128	0.0000	42.1128	0.0000	42.1128	0.0000
18	172	0.0365	43.8992	0.0000	43.8992	0.0000	43.8992	0.0000
19	179	0.0351	45.6856	0.0000	45.6856	0.0000	45.6856	0.0000
20	186	0.0338	47.4720	0.0000	47.4720	0.0000	47.4720	0.0000
21	193	0.0326	49.2585	0.0000	49.2585	0.0000	49.2585	0.0000
22	200	0.0314	51.0449	0.0000	51.0449	0.0000	51.0449	0.0000
23	207	0.0304	52.8313	0.0000	52.8313	0.0000	52.8313	0.0000
24	214	0.0294	54.6177	0.0000	54.6177	0.0000	54.6177	0.0000

Table 9: The location of the wires in the CDC. For each layer, we report the number of tubes, the angular rotation $\Delta\phi$ between tubes, and the (x, y) coordinates of the wire at three z positions. The up-stream pair (x_u, y_u) are on the inside face of the up-stream endplate ($z = 0$). The center pair are at the center of the chamber ($z = 0$), and the down-stream pair (x_d, y_d) are on the inside face of the down-stream endplate ($z = 150$). All distances are reported in cm and angles in radians.